



Quality Products. Service Excellence.

Liquid-Tight, Strain Relief Cordgrips *1427CG Series*

Features



- Black nylon, liquid-tight cordgrip.
- Used where cable is entering or leaving an enclosure.
- Accepts a wide range of cable diameters due to large opening and highly flexible strain relief elements, together with a TPE sealing ring.
- The strain relief elements tighten in a circular sequence on the sealing ring to give outstanding strain relief without twisting or damaging the cable.
- Use the cordgrip with the smallest maximum diameter that will fit your application (see table below).
- Nylon locknut included (as shown).
- Suitable for NEMA type 4 applications - Protection to IP68.
- UL94-V2 flammability rating.
- UL, CSA & VDE listed.



Part No.	Use With Wire Diameter		Mounting Hole Diameter
	Min	Max	
1427CG7	0.10	0.26	0.49
1427CG9	0.14	0.32	0.60
1427CG13	0.24	0.47	0.80
1427CG16	0.35	0.55	0.89
1427CG21	0.51	0.71	1.11

Data subject to change without notice

© 2018. Hammond Manufacturing Ltd. All rights reserved.