



Newer P/N- NWTU3S3HD

THE EASIEST WAY TO ACCESS DATA FROM ANY 2.5" OR 3.5" SERIAL ATA



hard drive not included

Voyager

- Data Access Now Made Simple!
- Boot and Swap Drives at Will
- Plug and Play, Hot Swap and add a new drive at anytime
- Choose Multi-Interface or USB 3.0 & 2.0 Interface

NEWEST GEN **MULTI-INTERFACE** DOCKING SOLUTIONS

HARD DRIVES UP TO **6.0TB**

WORKS WITH **MAC AND PC**

USB 3.0 / FireWire 800 / FireWire 400 / eSATA
interfaces
Mac and PC compatible

2 Year NewerTech Enclosure Limited Warranty
48-hour Warranty Service

Product Overview:

Voyager

NewerTech Voyager SATA drive docking solutions support all 2.5" & 3.5" SATA 6Gb/s, 3Gb/s & 1.5Gb/s drives up to 6.0TB.

BOOT AND SWAP DRIVES AT WILL

Whether you're on a data recovery mission or just want to check the contents of an older swapped out drive, NewerTech Voyager is the easiest, most convenient way to access data from any Serial ATA (SATA) drive. Just insert any standard 2.5" or 3.5" SATA I/II/III drive with up to 6.0TB capacity into the compact docking base and select one of the four interfaces supported by your Mac® or PC for the fastest data transfer performance. Then, start reading and/or writing data to the docked drive. There's nothing else to install or configure!

SAVE TIME AND MONEY

With its Plug and Play design, the NewerTech Voyager saves you the time of installing a drive into a computer or the cost of an external enclosure. Now you can think of bare SATA drives with the same convenience and instant access benefits as flash memory cards...but with huge gains in storage capacity!

HOT SWAP READY

Have multiple drives you need to access? No problem, NewerTech Voyager's unique design makes hot-swapping SATA drives a breeze*. When finished using your drive, simply pull up on it or use the eject lever for 3.5" drives for quick and effortless removal.

IDEAL SOLUTION FOR PHOTOGRAPHERS AND VIDEOGRAPHERS

Instead of needing multiple enclosures and power supplies for every archived drive, NewerTech Voyager makes accessing your valuable data a breeze. Just slide in your drive, find the desired image or clip, and then return the drive to your storage safe.

TRULY PLUG AND PLAY

With all supported interface connector cables included, an auto-switching power supply for worldwide compatibility, and flexible operating system compatibility, the NewerTech Voyager can travel your data universe with ease.

*Use of eSATA interface requires system reboot in order to recognize drive. For FireWire 800 users, OWC recommends that the Voyager be the only device connected or the last device in the chain when hot-swapping drives. If you have other devices behind the Voyager, not all devices will remount after a drive is swapped. When that occurs, a power-cycle is needed for that device. For eSATA users, a system reboot is required in order to recognize drive.

Product Features:

- Supports all 2.5" and 3.5" SATA I/II/III drives and SSD drives up to 6.0TB
- Multi-Interface for maximum data transfer rates and system compatibility
- Data transfer rates up to 5.0Gb/s (500MB/s)
- Push button drive eject for safe removal
- Hot-Swap functionality for fast access of multiple SATA drives
- Weighted base and non-skid rubber feet for stable operation
- 2-Color Status LED:
 - Left side Blue = Power
 - Right side Flashing Red = Disk Activity
- Compact design...measures 5.28" x 3.70" x 2.68" inches
- Whisper Quiet operation...no cooling fan needed
- Plug and Play with Macs and PCs
- All interface connection cables included
- RoHS Compliant
- 2 Year InterTech Enclosure Limited Warranty with 48-Hour Turnaround Time [Register Here](#)
- CE approved
- Transfer Rates:
 - USB 3.0: up to 5.0Gb/s (500MB/s)
 - eSATA: up to 3.0Gb/s (or 300MB/s)
 - FireWire 800: up to 800Mbps (100MB/s)
 - FireWire 400: up to 400Mbps (50MB/s)

Use of eSATA interface requires system reboot in order to recognize drive. For FireWire 800 users, OWC recommends that the Voyager be the only device connected or the last device in the chain when hot-swapping drives. If you have other devices behind the Voyager, not all devices will remount after a drive is swapped. When that occurs, a power-cycle is needed for that device. For eSATA users, a system reboot is required in order to recognize drive.

Product Specification:

Supports

- Serial ATA 1.5G/3G/6G (SATA I/II/III) Drives of 2.5" and 3.5" types and up to 6.0TB.
- Note: Voyager only accepts SATA interface drives (show connector) If you have IDE/ATA interface drives (show IDE), we recommend the [NewerTech USB Universal Drive Adapters](#).

Port/Interface Bootability

Can I use this solution as an external startup drive?

- eSATA: Supported on Macs and PC's meeting minimum requirements.
- FireWire 800: Supported on Macs and PC's meeting minimum requirements.
- FireWire 400: Supported on Macs and PC's meeting minimum requirements.
- USB 2.0: Supported on Macs and PC's meeting minimum requirements.

Features

- Push button drive eject for safe removal
- Hot-Swap functionality for fast access of multiple SATA drives
- 2-Color Status LED:
 - Left side Blue = Power
 - Right side Flashing Red = Disk Activity
- Whisper Quiet operation...no cooling fan needed
- RoHS Compliant
- CE approved

Bridge Chipset

- J Micron 562 and J Micron 355

Interface/Ports

- (1) eSATA port
- (2) FireWire 800 (1394b) ports
- (1) FireWire 400 (1394a) port
- (1) USB 3.0 port, fully backward compatible with USB 2.0

Maximum Data Transfer Rate

- eSATA - 3.0Gb/s (or 300MB/sec)
- FireWire 800 - 800Mbps (or 100MB/sec)
- FireWire 400 - 400Mbps (or 50MB/sec)
- USB 3.0 - 3.0Gb/s (or 300MB/sec)**

Macintosh Requirements

- Macintosh OS 8.6 to 9.2.2, OS X 10.2.x or later including 'Mavericks' 10.9.x, and an available FireWire, USB, or eSATA port. Time Machine® Compatible: Mac OS X 10.5 (version introduced) and later. Support for drives over 2TB requires Mac OS X 10.2 and later.

Macintosh Requirements

- Macintosh OS 8.6 to 9.2.2, OS X 10.2.x or later including 'Mavericks' 10.9.x, and an available FireWire, USB, or eSATA port. Time Machine® Compatible: Mac OS X 10.5 (version introduced) and later. Support for drives over 2TB requires Mac OS X 10.2 and later.

Linux Requirements

- Linux compatible via supported USB and FireWire interfaces.

Power Supply

- UL Listed U.S./International Auto Switching 100 ~ 240v, 50/60Hz input, 12 Volt 3 Amp output Power Supply (adapter plugs for International use [sold separately](#))

Material

- Weighted Base
- ABS black plastic with non-skid rubber feet

Dimensions

- 5.28" x 3.70" x 2.68" (W x D x H)
- 134.11mm x 93.98mm x 68.07mm

Weight

- 1.35 lbs. (.61kg) (without drive)

Warranty

- 2 Year NewerTech Enclosure Limited Warranty

Product Includes:

- NewerTech Voyager Q
- 2.5" & 3.5" SATA 6Gb/s, 3Gb/s or 1.5Gb/s drive connector
- Hinged flap for 3.5" drive access drive eject lever for safe removal of 3.5" drives
- Status LED:
 1. Blue = Power
 2. Flashing Red = Disk Activity



- Power receptacle
- USB 3.0 port
- eSATA port
- Two FireWire 800 (1394b) ports
- FireWire 400 (1394a) port
- UL Listed U.S./International Auto Switching 100 ~ 240v, 50/60Hz input, 12 Volt 3 Amp output Power Supply (adapter plugs for International use sold separately). For replacement power supply, [click here](#).
- 36" High Quality Double Shielded FireWire 800 connecting cable (9-9 Pin cable)
- 36" High Quality Double Shielded FireWire 400 connecting cable (6-6 Pin cable)
- 36" High Quality USB 3.0 (Standard-B to Standard-A) USB 2.0 backwards compatible cable
- 36" High Quality Double Shielded eSATA connecting cable
- 2 Year NewerTech Enclosure Limited Warranty with 48-Hour Turnaround Time.