

3/8 in. Keyless Chuck Adapter 16207

- 1/4" Hex Shank
- 3/8" Keyless Chuck conversion for 1/4" impact driver



UPC	Master	Inner
8-02090-16207-7	72	6

Right-Angle Drill Attachment 16235

- 90 Degree 1/4" Bit Driver
- 360 Degree Swivel Handle
- 1/4" Hex Shank
- 1/4" Chuck Bit Holder
- Smooth precision turning during 90 degree position



UPC	Master	Inner
8-02090-16235-0	48	6

3 pc. Damaged Screw Extractor Set 11215

- Includes (3) Double sided extractors: #1: Screw Size 4-7, SAE Bolt Size 7-32", MM Bolt Size 5mm, #2: Screw Size 8-10, SAE Bolt Size 1/4", MM Bolt Size 6mm, #3: Screw Size 11-14, SAE Bolt Size 5/16", MM Bolt Size 8mm
- For use with removing size 4-14 screws and bolts up to 5/16"
- Double sided extractor tips remove stripped screws and bolts
- Drill out, flip bit and extract screw



UPC	Master	Inner
8-02090-11215-7	144	12

10 pc. Screw Extractor/ Left Hand Drill Bit 16013

- 5 pcs Multi-fluted, machined alloy steel screw extractor. Sizes #1-5
- Remove broken screws easily
- 5 pcs left-hand cobalt drill bits. Sizes: 5/64", 7/64", 5/32", 1/4", 19/64"
- Metal storage box included



UPC	Master	Inner
8-02090-16013-4	48	12

Step Drills

- Drill multiple sizes with each bit

Part #	Contents/Size	UPC	Master	Inner
16503 3-pc Set	Bit one: 13 sizes from 1/8" to 1/2"; Bit two: 6 sizes from 3/16" to 1/2"; Bit three: 9 sizes from 1/4" to 3/4"	8-02090-16503-0	72	12
16501	#1 Bit 1/8" - 1/2"	8-02090-16501-6	144	24
16504	#2 Bit 1/4" - 3/4"	8-02090-16504-7	144	24

