

### Rare Earth Magnetic Hook 11138

- Diameter: 1-1/2"
- Holds up to 65lbs
- Strong neodymium magnet
- Hook swivels up and down, and rotates 360 degrees



UPC	Master	Inner
8-02090-11138-9	192	12

### Reversible Magnetic Hook 11139

- Diameter: 2-1/4"
- Holds up to 25lbs
- Loosen the bolt and flip the hook for versatility in hanging directions
- Use to hand lights, wiring, tools, banners, decorations and more from any ferrous metal surface



UPC	Master	Inner
8-02090-11139-6	96	12

### Magnetic Hooks

- Ideal for holding keys, tools, utensils, and more



Part #	Sizes	UPC	Master	Inner
11165 2-pc 8lbs	1-7/16in	8-02090-11165-5	192	12
11166 2-pc 15lbs	2in	8-02090-11166-2	96	12



Part #	Sizes	UPC	Master	Inner
11167 15lbs	2-1/2in	8-02090-11167-9	96	12
11168 40lbs	3in	8-02090-11168-6	96	12

### 1/2 in. x 30 in. Flexible Magnetic Tape Roll 11197

- Dimensions: 1/2" wide x 30" long
- Can be easily cut to desired length
- Adhesive on one side, magnetic on the other



UPC	Master	Inner
8-02090-11197-6	72	12

### Magnetizer-Demagnetizer 11145

- To Magnetize: insert tool in and out of the + chamber
- To Demagnetize: Insert tool in and out of the lowest step in the - chamber
- If tool is still magnetized, repeat on a higher step



UPC	Master	Inner
8-02090-11145-7	96	1