



3 pc. 1/4 in. Drive Finger Grip Drivers 11218

- Size includes: (1) 1/4in slotted screwdriver bit, (1) #2 Phillips screwdriver bit, (1) 1/4in socket adapter
- Knurled for easier grip
- Interchangeable bits

UPC	Master	Inner
8-02090-11218-8	96	12

12 pc. 18 in. Extra-Long Ratcheting Screwdriver 12218

- High-torque for maximum utility: 250 in-lbs (35 kg/m)
- Bits included: (3) Phillips bits, sizes: #1, #2, and #3, (4) Slotted bits, sizes: 5/32", 3/16", 1/4", and 9/32", (2) Star bits, sizes: T15 and T20, (1) Square bit, size: SQ2
- Set also includes (1) 1-1/4 in. socket adapter
- Reversible ratcheting design
- Magnetic bit holder
- Bit storage in handle
- Bits made of S2 steel
- Overall Length: 18 in.



UPC	Master	Inner
8-02090-12218-7	36	6





- Set Includes: (3) Phillips: #1,#2,and #3, (4) Slotted: 5/32, 3/16. 1/4, and 9/32 inch, (2) Star: T15 and T20, (1) Square: SQ2, (1) 1-1/4" Socket Adapter
- High Torque 250 in-lbs (3 kg/m)
- Flex-head, 20 degree angle
- Reversible ratcheting design
- Convenient bit storage in handle
- Bits made of S2 steel
- Overall Length: 10 in.



12 in. High Torque Ratcheting Screwdriver 12220

- High Torque 250 in-lbs (35 kg/m)
- Set Includes: (3) Phillips: #1, #2, & #3, (4) Slotted: 5/32", 3/16", 1/4", & 9/32", (2) Star: T15 & T20, (1) Square: SQ2, (1) 1-1/4" Socket Adapter
- Reversible ratcheting design
- Stainless steel shaft
- Bit storage in handle
- Bits made of S2 steel
- Overall Length: 12"

