

Testing tools
Combi Check 2MM

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



The main function of the voltage tester is to establish if voltage is present. A 2-pole voltage tester is the only approved testing instrument that fulfils the requirements of work protection regulations.

- with LED-Display
- acc. to VDE standard
- high peak voltage strength
- the right tester for every application

General ordering data

Type	Combi Check 2MM
Order No.	9204230000
Version	2-pole voltage tester type 1156, Yes - visual + acoustic
GTIN (EAN)	4032248616497
Qty.	1 pc(s).

**Testing tools
Combi Check 2MM**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Weight	290 g	Net weight	204 g
--------	-------	------------	-------

Measuring and testing devices

AC voltage display	6, 12, 24, 50, 120, 230, 400, 690 V	AC voltage measuring range	6-690 V
Battery type	1.5 V type AAA battery	Continuity test	Yes - visual + acoustic
DC voltage display	6, 12, 24, 50, 120, 230, 400, 690 V	Display	LED
Frequency range, max.	100 Hz	Frequency range, min.	0 Hz
Insulation test	6 kV	Measuring range category	CATIV - 400V/ CAT III - 690V
Operating temperature, max.	45 °C	Operating temperature, min.	-15 °C
Peak voltage resistance	8 kV	Protection degree	IP65
Rated voltage, max.	690 V AC/DC	Rated voltage, min.	6 V

Classifications

ETIM 5.0	EC000494	ETIM 6.0	EC000494
eClass 6.2	27-20-03-08	eClass 7.1	27-20-03-08
eClass 8.1	27-20-03-08	eClass 9.0	27-20-03-08
eClass 9.1	27-20-03-08		

Product information

Descriptive text technical data	Buzzer included
---------------------------------	-----------------

Approvals

Approvals



ROHS	Conform
------	---------

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
--------------------	--------------------------------------