

Screwty M8F KO o. SD**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



The Screwty® attachment is suitable for customisable M8 round plug-in connectors, with an outside dimension of the knurled nut of 11.9 ± 0.3 mm. The tightening torque is 0.5-0.6 Nm.

General ordering data

Type	Screwty M8F KO o. SD
Order No.	1900130000
Version	Tools, Cable gland tool for M8 connectors
GTIN (EAN)	4032248431267
Qty.	1 pc(s).

Screwty M8F KO o. SD

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

Net weight 15 g

Classifications

ETIM 4.0	EC002556	ETIM 5.0	EC002556
ETIM 6.0	EC000149	UNSPSC	27-11-17-02
eClass 5.1	21-04-01-90	eClass 6.2	21-04-01-90
eClass 7.1	21-04-01-90	eClass 8.1	21-04-01-90
eClass 9.0	21-04-01-90	eClass 9.1	21-01-90-90

Approvals

ROHS Conform

Downloads

Brochure/Catalogue [CAT 6 TOOLS 15/16 EN](#)
[CAT 8 SAI 15/16 EN](#)
[FL FIELDWIRING EN](#)