

Energizer® Vision HD Headlight

HDB321


The *Energizer*® Vision HD headlight is another innovative headlight solution from the *Energizer* premium headlight line. With the latest LED technology, users get an extremely bright, lightweight hands-free solution with ample run time capability. Patented optics offer exceptional direct and peripheral vision, making the *Energizer* Vision HD a perfect light for home, work and outdoor activities. Thanks to *Energizer*® Smart Dimming technology, users can control the intensity of light from 100% to 10%, and enjoy Next Push Off technology to avoid unnecessary switch cycles. With an adjustable head strap, water-resistant design and pivoting head to direct light exactly as needed, this headlight is another way *Energizer* continues to deliver innovative lighting solutions.



Provides 180 Lumens of Light




Provides Run Time of 8 Hours



Shines Light on Objects up to 40 Meters Away



Sustains 1 Meter Drop Test



Works even after splashing water on all sides.

DESIGN BENEFITS

- ✓ *Energizer*® Smart Dimming technology to control light intensity
- ✓ Next Push Off to avoid unnecessary switch cycles
- ✓ Weather-resistant design
- ✓ Shatterproof lenses
- ✓ Pivoting head to direct light where needed

LIGHT AND POWER SOURCE

- ✓ Features LED Technology
- ✓ Operates on 3 AAA Batteries

CERTIFICATES AND COMPLIANCE

CE RoHS

EMC, EN62471, FCC



Tested according to ANSI/NEMA FL1 Standards. Results based on: *Energizer*® MAX, Alkaline / E92

PERFORMANCE BENEFITS

- ✓ Up to 4X brighter than standard LED technology
- ✓ Patented optics, delivering exceptional direct and peripheral vision
- ✓ Long runtime

SPECIFICATIONS

Weight Excluding Batteries:

52 Grams / 1.83 Ounces

Dimensions:

59mm x 49mm x 36mm / 2.3" x 1.9" x 1.4"

NUMBER OF OPERATING MODES: 4

Mode	Lumens (Lm)	Runtime (h)	Beam Distance (m)
High	180	8	40
Low	30	49	-
Spot	145	13	-
Flood	70	30	-