

# Energizer®

Outdoor



## VISION HD+ HEADLIGHT

Innovation that delivers performance,  
mobility and vision





New and improved vs. previous range,  
Up to **4X brighter** vs. ordinary LED's



## VISION HD+ HEADLIGHT

- 3 white LEDs
- 2 red LEDs
- Spot & Area light modes
- Dimming
- Next push off
- Adjustable elastic headband
- Pivoting head
- Shatter proof lens
- Weatherproof
- Survives a 1 meter drop
- Designed to last 15 years
- 3 x AAA Alkaline batteries included



Brightness



Runtime<sup>1</sup>



Beam Distance



Weatherproof<sup>2</sup>

SPECIFICATIONS	SAP/GMN	E300280601
	MODEL	HDC321
	EAN	7638900316384
	ITF	17638900316381
	TORCH CU/SU	1/6
	DIMENSIONS CU (mm) (H,W,D)	190.5 x 147.3 x 39.4
	DIMENSIONS SU (mm) (H,W,D)	203.2 x 282.575 x 161.925
	WEIGHT (Kg) CU/SU	0.118/0.930
	SU DETAILS	Single facing tray
	BATTERIES	3 x AAA
	BULB	3 x White LED & 2 x Red LED



<sup>1</sup>Based on a fresh set of Energizer® Max® AAA batteries. <sup>2</sup>Weatherproof to IPX4 (not submersible)

FOR MORE INFORMATION ON ALL OUR LIGHTING  
PRODUCTS VISIT: [www.energizer.eu](http://www.energizer.eu)