

DRILL ACCESSORIES

SHOP/GARAGE

90° IMPACT DRIVER ATTACHMENT

- Magnetic 1/4" hex adapter accepts standard drill and driver bits.
- Die-cast gear housing and 3 sets of ball bearings.
- Works in forward or reverse.

Item #	IP	MP	PKG	Shank	Length
W9029	15	60	CRD	1/4"	6"



Impact driver attachment lets you use 1/4" quick connect bits in tight spaces.

QUICK RELEASE BIT EXTENSION

- 1/4" hex fits standard drills, drivers and screwdrivers.
- Magnetic bit holder keeps bits in place.
- Auto-locking quick release chuck.

Item #	IP	MP	PKG	Shank	Length
W8603	6	72	TAB	1/4"	6"



Easy to hold rotating sleeve.

SCREWDRIVER BITS & HOLDER

- Heat treated for durability.

Item #	IP	MP	PKG	Shank	Length	Sizes
W8598	5	240	CRD	1/4"	2"	1/4", #2
W3219	50	600	Pg 315	1/4"	2"	#2
W3220	50	600	Pg 315	1/4"	2-1/4"	-



W3219

W3220

IMPACT BIT SET

- Impact grade chrome vanadium steel.
- Heat-treated to resist breakage.

Item #	IP	MP	PKG	Shank	Length	Sizes
W472	5	240	CRD Pg 318	1/4"	2"	2ea: #2, 1/4", S1, S2



W472

3-PC MAGNETIC NUT SETTER

- Powerful magnet holds fasteners, freeing up your hands in tight spaces.
- Lobular drive prevents rounding
- 1/8" insert depth.

Item #	IP	MP	PKG	Shank	Length	Sizes
W9022	12	96	CRD	1/4"	2-1/2"	1/4, 3/8, 5/16"



W9022

14-PC NUT DRIVER BIT SET

- Compact bit holder with belt clip
- Hardened chrome vanadium with black phosphate finish

Item #	IP	MP	PKG	Shank	Length	Sizes
W473	10	40	CRD Pg 318	1/4"	2"	3/16, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16" 5, 5.5, 6, 7, 8, 10, 12mm



3-PC POWER DRILL SOCKET ADAPTER SETS

- Transforms your power drill into a power nut/socket driver.
- Impact grade chrome vanadium steel.
- Ball bearing ensures sockets are securely seated.
- 1/4, 3/8 and 1/2" drive sizes.



W9026

Item #	IP	MP	PKG	Shank	Length	
W1390	12	96	CRD	1/4"	2"	
W9026	6	48	CRD	1/4"	6"	
W9030	6	48	TAB	1/4"	2"	30° Wobble

30° taper provides increased angle flexibility for hard to reach areas.

W9030