

SOLDERING KITS

- Nickel plated tip gives longer life and more efficient soldering.
- Built in spotlight.
- Instant heat.
- cUL listed E231844



Item #	IP	MP	PKG	Watt	Amp	Temp °F	Length	AWG	Listing		
W2012	5-PC	6	24	DBL	60W	.8A	1,135	4.5'	18/2	cUL	Gun, wire, paste, two tips
W2019A	4-PC	6	24	CBX	85W	.7A		4.5'	18/2	cUL	Gun, wire, two tips
W2013	2-PC	6	48	CRD	30W			4.4'	18/2	UL	Pencil, tool rest
W2012-1	2-PC	12	72	CRD	Replacement tips for W2012						

CORDLESS SOLDERING IRON

- Heats up to working temperature in under 15 seconds and cools down instantly.
- Equivalent to an 8W soldering iron.
- LED power indicator.
- Continuous runtimes:
45 min on low, 30 min on high.



Item #	IP	MP	PKG	Power	Temp °F	Battery	
						Qty.	Type
W2000	6	24	DBL	8W*	572	3	AA
W2000-1	24	288	CRD	Replacement tip			

LEAD FREE SOLDER

- 0.031" Rosin core solder for any application.
- Lead free solder - 99.3% tin, 0.7% copper.
- 10' (3.0m) roll in storage tube.



Item #	IP	MP	PKG	Thick	Length
W3248	12	144	Pg 318	0.031"	10'

HELPING HANDS

- Adjustable ball joints position and hold work at any angle
- Two alligator clamps hold light materials steady
- 2X, 2-1/2" magnifying glass for precision work
- Heavy duty cast iron base

Item #	IP	MP	PKG
W2010	6	24	DBL

MINI FLAME THROWER

- Refillable with an adjustable flame.
- Melts solder, gold, small brazing rod, tin and much more.

Item #	IP	MP	PKG	Temp °F
W2002	6	24	DBL	2,500