

INDUSTRIAL SHOP CART

- Easy rolling utility cart with upper and lower trays.
- 2 shelf utility cart holds up to 500 lbs. total but is light weight and maneuverable.
- Industrial duty polypropylene construction won't rust, dent or chip.
- 5" Diameter non marring casters, (two locked and two swivel).



Tool utility cart has tool storage and cup holder on the handle.



Item #	IP	MP	PKG		Width	Depth	Height
W53991	1	1	CBX	Cart	17"	39-3/4"	33-1/4"
				Trays	16"	30"	3"

3 WHEEL MOVERS DOLLY

- Soft cushions protect objects being moved.
- Depressed center for objects with legs.
- Holds up to 132 lbs. evenly distributed.
- 1-1/2" casters for easy maneuvering.



Item #	IP	MP	PKG
W54038	6	36	CBX

UNIVERSAL WELDING CART

- All steel construction with durable finish.
- 7-1/2" back wheels and 3" front swivel castors makes the welding cart very easy to move around.



Item #	IP	MP	PKG
W53992	1	1	LAB

STEEL HAND TRUCK

- Heavy duty design,
- 18 gauge 1" steel tube frame.
- Durable powder coated finish.
- 10" 4 ply pneumatic tires.
- Extra large 14 x 7-1/2" toe plate.
- 600 lbs. load capacity.



Item #	IP	MP	PKG	Width	Depth	Height
W41060	1	1	LAB	21"	17-1/2"	51-1/2"