

## DIGITAL MICROMETER

- Reads both SAE and Metric dimensions to an accuracy of 1/10,000th of an inch, and 0.0025mm.
- C2 carbide ground anvil and spindle for added durability and accuracy.
- Measures up to 1" (25mm) in an easy to read LCD screen.
- Includes rolling measurement adapter, battery and storage/carrying case.



Item #	IP	MP	PKG	Max Range		Resolution		Accuracy ±		Overall Length	Battery	
				inch	mm	inch	mm	inch	mm		Qty.	Type
W80156	5	50	SLV	1	25	0.00005	0.001	0.0001	0.0025	6-1/8"	1	SR44

## DIGITAL SCALES

- Digital LCD screen clearly shows weight in pounds, kilograms or \*stones.
- Provides accurate readings up to 660 lbs. (300Kg).



W1477

Strong and comfortable handle.



W1478

Strong steel S-hook and O-ring to connect to hoist or gable

Item #	IP	MP	PKG	Units	Capacity	Accuracy	Battery	
							Qty.	Type
W1477	6	24	CRD	lbs, Kg	100 lbs.	-	1	CR2032
W1478	6	24	CBX	lbs, Kg, St	660 lbs.	±0.2 lbs.	2	CR2032

## INFRARED THERMOMETERS

- Measures surface temperature without making contact.
  - Easy to read large digital display with backlight.
  - Laser pointer for accurate use.
  - Fahrenheit or Celsius readings.
  - Includes a 9V battery.
- (except W89721 2-AAA batteries)



W89721



Item #	IP	MP	PKG	Temperature Range		Distance Spot Ratio	Accuracy
				°F	°C		
W89720	5	20	CLM	0 to 960	-18 to 520	8:1	±1.5%
W89721	10	20	CLM	-58 to 716	-50 to 380	12:1	±1.5%
W89722	10	60	CLM	-58 to 626	-50 to 330	12:1	±1.5%
W89724	5	10	CLM	-58 to 1382	-50 to 750	12:1	±2%

## DIGITAL LASER TACHOMETER

- Use to accurately measure the RPM without touching the object, displays it on a LCD screen.
- Measures the rotational speed with a visible red LED beam.
- High intensity class II laser measures from 2.5 - 99,999 RPM.
- Auto zero adjustment, stores last, minimum and maximum readings.
- Includes a handy storage case, 9v battery, 24" of reflective tape to aid measurements and operating manual.



Item #	IP	MP	PKG	Testing Range (RPM)	Resolving Power (RPM)	Accuracy	Sampling Time	Battery	
								Qty.	Type
W89719	1	50	DBL	2.5 to 99,999	0.1 (2.5 to 999.9)	±0.05%	0.8s	1	9V

HAND TOOLS