

8 PC JUMBO SCREW EXTRACTOR SET

#53100



-Use with wrench to remove broken and stripped screws. -Drop forged, heat treated carbon steel. -Tapered counter clockwise threads. -Sizes: #1, #2, #3, #4, #5, #6, #7, #8. -Case pack: 12.

40 PC TAP & DIE SETS

#53202 - MM
#53222 - SAE



-Drop forged, heat treated, tempered high carbon steel. -Tap and dies provide clean, straight, easy threading. -Precision machined to exacting standards. -Case pack: 12.

45 PC TUNGSTEN TAP & DIE SETS

#53280 - MM
#53300 - SAE



-Tap and dies provide clean, straight, easy threading. -Heat treated, rust resistant, tungsten steel with satin finish. -Precision machined. -Rockwell hardness of 58-61 HRC. -Case pack: 2.

LED TELESCOPIC INSPECTION MIRROR

#55117



-Dual ball joint positions the large mirror at any angle. -Twin LED lights illuminate hidden areas. -Double dipped grip handle with stainless steel shaft extends 11" to 34". -Case pack: 36.

4 PC LOCKING PLIERS SET

#56027



-Drop forged, heat treated, serrated steel jaws. -Thumb screw knob adjusts lock jaw capacity. -Includes - 5" and 7" curved jaw pliers, 10" straight jaw pliers, and 6" long nose pliers. -Case pack: 12.

2 PC MINI LOCKING PLIERS SET

#56030



-Use for intricate repairs where ordinary sized pliers cannot reach. -Drop forged, heat treated steel; nickel plated to resist corrosion. -Includes: locking pliers, long nose locking pliers. -Case pack: 36.