

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0879332415**
Status: **Active**
Overview: Slim-Grid Board-to-Board Connectors
Description: Slim-Grid Header, 24 Circuits, Surface Mount, Vertical, Unshrouded, 0.05µm Overall Gold (Au) Plated, with Pick-and-Place Cap, Tube, Lead-Free

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification 879330001-000 \(PDF\)](#) [Product Literature \(PDF\)](#)
[Packaging Specification PK-89990-565-000 \(PDF\)](#)

General


Product Family	PCB Headers
Series	87933
Application	Board-to-Board, Signal
Comments	4.3 Amps per Pole with only 1 contact powered up 1.4 Amps per Pole with max contacts powered up
Overview	Slim-Grid Board-to-Board Connectors
Product Literature Order No	987651-5972
Product Name	Slim-Grid
UPC	191128088343

Physical

Breakaway	Yes
Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	500
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Material - Resin	Liquid Crystal Polymer
Net Weight	0.408/g
Number of Rows	2
Orientation	Vertical
PCB Locator	No
PCB Retention	None
Packaging Type	Tube
Pitch - Mating Interface	1.27mm
Pitch - Termination Interface	1.27mm
Plating min - Mating	0.051µm
Plating min - Termination	0.051µm
Polarized to Mating Part	No
Polarized to PCB	No
Robotic Placement	Pick and Place Cap
Shrouded	No
Temperature Range - Operating	-55°C to +105°C
Termination Interface: Style	Surface Mount

Electrical

Current - Maximum per Contact	1.4A
-------------------------------	------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[87933](#) Series

Mates With

Slim-Grid Receptacle (Gold Plated) [78120](#)

Voltage - Maximum 125V AC

Solder Process Data

Duration at Max. Process Temperature (seconds) 011

Lead-free Process Capability REFLOW

Max. Cycles at Max. Process Temperature 001

Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Packaging Specification PK-89990-565-000

Product Specification 879330001-000

Sales Drawing SD-87933-0001-000

This document was generated on 07/27/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION