



## MPX-622/SW

Order No.: 20.2210

**Price upon request**

### PRODUCTINFOS

#### **6-channel stereo audio mixer,**

particularly suitable for PA and DJ applications.

- 2 mono microphone channels with talkover switch and 2-way tone control
- 4 stereo input channels, switchable phono/line (channels 1 and 2) or line/line (channels 3 and 4)
- 1 stereo master output
- 1 stereo record output, independent of the master
- 3-way equalizer with centre click for master output and record output
- Pre-fader listening to each stereo input channel and the master output via adjustable stereo headphone output
- Switchable crossfader for crossfading between channels 1-4, any assignment possible
- Stereo LED level display

### TECHNICAL SPECIFICATIONS

#### **MPX-622/SW**

No. of channels	6
No. of inputs	8
Mic input	1 mV, 2 x 6.3 mm jack
Line input	150 mV, 5 x RCA L/R
CD input	150 mV, 1 x RCA L/R

**MPX-622/SW**

Phono input	3 mV, 2 x RCA L/R
Master output	0.775 V/600 $\Omega$ , 1 x RCA L/R
Record output	0.775 V/600 $\Omega$ , 1 x RCA L/R
Headphones	$\geq 8 \Omega$ , 1 x 6.3 mm jack
Frequency range	20-20,000 Hz
THD	0.1%
S/N ratio	65 dB
Equalizer bass	$\pm 10$ dB/100 Hz
Equalizer midrange	$\pm 10$ dB/1 kHz
Equalizer treble	$\pm 10$ dB/10 kHz
Talkover	-15 dB
Crossfader	yes
Power supply	$\sim 230$ V/50 Hz/10 VA
Mains voltage	$\sim 230$ V
Mains frequency	50 Hz
Power consumption, operation	10 VA
Admiss. ambient temp.	0-40 $^{\circ}$ C
Width	482 mm
Height	89 mm
Depth	95 mm
Rack spaces, RS	2
Weight	2.4 kg