

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936000037](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Plastic Cable Gland, with Washer and Gaskets, M20x1.5 Thread, Grey](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93600
Cable Gland Type	IP66 - Basic
Comments	4 Gaskets: 4.00, 7.00, 10.00, and 13.00mm internal diameters.
Exclude SD Check	Yes
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Cable Glands
Product Name	GWconnect
UPC	887191824390

Physical

Cable Diameter	3.50-12.50mm
Flammability	UL 94V-0
Gland Color	Light Grey RAL 7035
Material - Cable Gland	Polyamide
Material - Gasket	Elastomer
Material - Plating	Zinc (washer)
Material - Washer	Steel
Net Weight	11.000/g
Packaging Type	Bag
Temperature Range - Operating	-40° to +125°C
Thread Size	M20x1.5
Thread Type	(M) Metric

Material Info

Engineering Number	7000.6839.0
--------------------	-------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93600 Series](#)

Use With

Plastic Enclosures Size 3A «21x21»