



- NOTES:
- MATERIAL: NYLON 6/6 UL 94 V-2 (RMS-01).
 - FLAME RETARDANT NYLON 6/6 UL 94 V-0 (RMS-19),
 AVAILABLE BY SPECIAL ORDER ONLY.
 - HEAT RESISTANT NYLON (RMS-109),
 AVAILABLE BY SPECIAL ORDER ONLY.
 - COLOR: NATURAL.
 - PART DESIGNED IN INCHES, METRIC CONVERSION FOR REFERENCE ONLY

PART NO. FOR #4 (M3) SCREW	PART NO. FOR #6 (M3.5) SCREW	PART NO. FOR #8 (M4) SCREW	DIM. "A" ±.015 [0.4]
SRS4-2-01	----	----	1/8 [3.2]
SRS4-3-01	----	----	3/16 [4.8]
SRS4-4-01	SRS6-4-01	SRS8-4-01	1/4 [6.4]
SRS4-5-01	SRS6-5-01	SRS8-5-01	5/16 [7.9]
SRS4-6-01	SRS6-6-01	SRS8-6-01	3/8 [9.5]
SRS4-7-01	SRS6-7-01	SRS8-7-01	7/16 [11.1]
SRS4-8-01	SRS6-8-01	SRS8-8-01	1/2 [12.7]
SRS4-10-01	SRS6-10-01	SRS8-10-01	5/8 [15.9]
SRS4-12-01	SRS6-12-01	SRS8-12-01	3/4 [19.1]
SRS4-14-01	SRS6-14-01	SRS8-14-01	7/8 [22.2]
SRS4-16-01	SRS6-16-01	SRS8-16-01	1 [25.4]

SERIES NO.	"B"	"C"	MOUNTING HOLE DIA. ±.003 [0.08]
SRS4	1/4 [6.4]	.125 [3.2]	.187 [4.7]
SRS6	9/32 [7.1]	.153 [3.9]	.234 [5.9]
SRS8	9/32 [7.1]	.169 [4.3]	.234 [5.9]

F			SEE ECN #1070 FOR CHANGES	SK	10/07/05	TITLE: SELF RETAINING SPACERS				DWG IN IN [MM]		
-			SEE ENGINEERING FOR REV. A - E	-	----	CREATED USING SOLIDWORKS	FILE #: SRS	DWN: SK				APP: RT
REV.			DESCRIPTION	ENGR.	DATE	TOLERANCES UNLESS NOTED .XX=±.010 .XXX=±.005 FRAC.=±1/64 ANG.=±1°	SHEET: 1 OF 1	SHEET SIZE: A	DT: 09/28/05	CHKD: SJ	PART # SEE TABLE	PRINT TYPE CA
						RE: RICHCO, INC.	RICHCO, INC. ENG@RICHCO-INC.COM (773) 539-4060					