

RoHS
Compliant



Features

- Lightweight and Portable
- Inspects USB Charger & Portable Power Source
- LCD Backlight
- High/Low Output Voltage Warning

Electrical Specifications

Parameter	Range
Voltage Measurement (DC)	3.0V - 9.0V $\pm 1\%$
Current Measurement (DC)	0.0A - 3.0A $\pm(1\% \pm 2 \text{ digits})$
Energy	0 - 9999mAh
Memory	10 Sets of Data

General Characteristics

Colour : White
Weight : 28g
Dimensions : 84mm \times 29mm \times 12mm

Accessories

Blister and Insert Card

Part Number Table

Description	Part Number
USB Tester	72-13540

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.