VGA LINK TESTER

72-9270 is VGA link tester. 72-9270 can test the signal of PC to VGA monitor / TV It is standard HDD-15 to HDD-15 link tester. 72-9270 use 9 pcs LED to show the test result.

Pin assignment (full pin test)

HD15 Female <=> HD15 Female	Signal	Text	LED-Color	Test
1 <=> 1	Red	R	Red	75R-Termanate
2 <=> 2	Green	G	Green	75R-Termanate
3 <=> 3	Blue	В	Blue	75R-Termanate
4 <=> 4	ID2	ID2	Green	Signal
11 <=> 11	ID0	ID0	Green	Signal
12 <=> 12	ID1	ID1	Green	Signal
13 <=> 13	HSYNC	HS	Red	Signal
14 <=>14	VSYNC	VS	Red	Signal
15 <=> 15	ID3	ID3	Green	Signal
5/6/7/8/10	GND			
<=>5/6/7/8/10				
9<=> 9	NC			

Specification:

- 1. No power required & test VGA interface.
- 2. With extend function --- VGA Female / Female Changer.
- 3. Support VGA on line Simple test. Support plug& play.
- 4. With 3 colors LED appeared, easy to check data transfer & receiver.
- 5. On line test: VGA band width: over 450Mhz (1600*1200)

Connection:



