



Part Number: PDWM4350U

Description: UHF Wireless Microphone System Kit, Adjustable Frequency, Includes (2) Handheld Mics, (2) Beltpack Transmitters, (2) Lavalier Mics & (2) Headset Mics

Product Description

The Pyle PDWM4350U delivers clear, noise-free, wireless transmission and excellent sound reproduction. The Pyle PREMIER Series Wireless Microphone Systems are easy-to-install and easy-to-operate. System features (4) individual balanced XLR outputs and (1) unbalanced jack. Also includes (2) Handheld Mics, (2) Belt Pack Transmitters, (2) Lavalier Mics and (2) Headset Mics. Whether used for work or play, for on-stage vocal performances, or conference room speeches, this rack mountable wireless microphone system will give you an amazing high-quality audio experience. Enjoy hassle-free and reliable wireless sound transmission with today's latest system technology with this all-in-one package.

Features:

- UHF Band Receiver System
- Quad Frequency 4-Channel Design (Channel 1, 2, 3, 4)
- Broad Frequency Response Range & Low Distortion
- High Signal/Noise Ratio Performance
- RF Signal & AF Signal LED Indicators
- LCD Digital Display with Channel & Frequency Readout
- Independent Channel Adjustable Volume Controls
- Easy-to-Use Touch Button Controls
- Detachable Dual Antennas
- Rack Mountable System

• What's in the Box:

- 4-Ch. Microphone Receiver
- (2) Handheld Microphones

- (2) Beltpack Transmitters
- (2) Headset Microphones
- (2) Lavalier Microphones
- (8) 'AA' Batteries
- Detachable Rack-Mount Hardware
- Wall Power Adapter

- **Handheld Microphone Specs:**

- RF Output: 10dBm
- Modulation Type: FM
- Max Deviation: ± 40 KHz
- Spurious Emission: >55 dBc
- Battery Powered, Requires (2) x 'AA' Batteries -Each
- Microphone Dimensions: 9.4" x 2.0" x 2.0" -inches

- **Bodypack Transmitter Specs:**

- RF Output: 10dBm
- Modulation Type: FM
- Max Deviation: ± 40 KHz
- Spurious Emission: >53 dBc
- Battery Powered, Requires (2) x 'AA' Batteries -Each
- Bodypack Dimensions: 4.1" x 2.6" x 1.2" -inches

- **4-Channel Base Receiver Specs:**

- Image & Spurious Rejection: >70 dB
- Receiving Sensitivity: -105 dBm
- Signal/Noise Ratio: >85 dB
- Border Upon Channel Rejection: >70 dB
- T.H.D.: $<0.5\%$
- Audio Output Level: 0-300mV
- Power Supply: 110/220V (12-15V Power Adapter)
- Receiver Dimensions: 15.5" x 8.0" x 2.0" -inches

- Sold as: Unit
- Weight: 7.9 lbs.

