

NEBO®
REBEL™



The REBEL is a fully rechargeable task light that includes an adjustable head strap for use as a head lamp. Small enough to fit in the palm of your hand, this powerful light rebels against its size with its impressive 600 lumen output. This bright light is also equipped with a rotating, removable steel clip and powerful magnetic base to provide even more hands-free lighting options.



- 4 LIGHT MODES**
- HIGH (240 lumens) - 2 hours / 56 meters
 - LOW (60 lumens) - 4.5 hours / 28 meters
 - TURBO (600 lumens) - 40 seconds / 90 meters
 - STROBE (600 lumens) - 2 hours / 90 meters

DESIGN

- Fully rechargeable
- Removable steel clip
- Anodized aircraft-grade aluminum; water and impact-resistant

OPERATION

- Top-positioned, ON/OFF button

ACCESSORIES

- Adjustable head strap; one size fits all
- Magnetic USB to Micro USB charging cable with charging indicator included

BATTERIES

- Powered by rechargeable battery (included) (Recharge time: 1.5 - 2 hours)

SPECS

- 0.1875 lbs.
- (H) 2.85" x (W) 1.2" x (D) 1"



Display Dimensions
(H) 11.5" x (W) 10.75" x (D) 13.75"

Gift Box Dimensions
(H) 5.25" x (W) 3.25" x (D) 2.45"

UPC CODE	ITEM	DESCRIPTION
645397932369	6691	REBEL 600 Lumen Task Light / Head Lamp

NEBO®
DUO 250+ LUMEN
HEAD LAMP

The NEBO® DUO Head Lamp is an all-powerful, hands-free lighting solution. The push button on/off button allows you to easily cycle through the FOUR light modes: one white LED (250 Lumens), 2 C•O•B strips (80 Lumens) or 2 RED C•O•B strips in steady or beacon mode. The red LED is a low-signature light, which ensures stealth in the dark, enhances night vision and makes reading in little to no light possible. Its signature 2 strip C•O•B design fully illuminates your immediate area with its wide flood beam. The DUO Head Lamp is tough, reliable, lightweight and completely shock-proof.

4 LIGHT MODES

- Spot Light (250 lumens) - 3.5 hours / 122 meters
- C•O•B Flood Light (80 lumens) - 7 hours / 13 meters
- Red C•O•B (10 lumens) - 8 hours / 4 meters
- Red Beacon - 48 hours / visible over 1 mile

DESIGN

- Fully dimmable
- Water and impact-resistant durable housing
- 90° tilt
- Power memory setting
- Direct-to-red feature

OPERATION

- Top-positioned, ON/OFF button

ACCESSORIES

- Dual adjustable head strap; one size fits all

BATTERIES

- Powered by 3 AAA batteries (included)

SPECS

- 0.2 lbs.



Display Dimensions
(H) 12.5" x (W) 6.625" x (D) 10"

Clamshell Dimensions
(H) 6.125" x (W) 5.25" x (D) 3"

CALIFORNIA REQUIRED ⚠️ WARNING
Cancer and Reproductive Harm
www.P65Warnings.ca.gov/product

UPC CODE	ITEM	DESCRIPTION
645397930983	6444	DUO 250+ Lumen Head Lamp