


13 82 200 T

Pliers for Electrical Installation with tether attachment point



- Multifunctional pliers for the electrical installation; to grip flat and round material, for bending, deburring, cutting cable, stripping and crimping end sleeves (ferrules)
- 6 functions in one pair of pliers
- Smooth surfaces near the tips grip single cores without damaging them; serrated gripping surfaces and pipe grip for gripping flat and round material
- Clear-cut outside edge on the jaw for working on flush-mounted junction boxes and deburring feed-through holes
- Stripping holes for conductors of 0.75 - 1.5 mm² and 2.5 mm²
- Crimp die for wire-end ferrules 0.5 - 2.5 mm²
- Cable shears with (induction-hardened) precision cutting edges for copper and aluminium cables up to 5 x 2.5 mm² / dia. 15 mm
- Gripping, without opening the pliers completely (intelligent latching mechanism in the spring assisted version). The cutting edge remains closed and protected
- Slim dimensions for easy access
- Bolted joint: precise, zero backlash operation of pliers
- High-grade special tool steel, forged, multi stage oil-hardened
- Pliers with tether attachment point for mounting a fall protection

Article No.	13 82 200 T
EAN	4003773079972
Pliers	black atramentized
Head	polished
Handles	with multi-component grips, with integrated tether attachment point for a tool tether
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	15
Cutting capacity copper cable, multiple-stranded mm²	50
Stripping capacity for cross-sections mm²	0,75 - 1,5 + 2,5
Capacity in square millimetres mm²	0,5 - 2,5
AWG	1/0
Length mm	200
Net weight g	267



technical change and errors excepted