

64 12 115

Electronics End Cutting Nipper



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened, cutting edge hardness at least 56 HRC
- High-grade special tool steel, forged, multi stage oil-hardened
- End Cutter, with small bevel



Article No.	64 12 115
EAN	4003773040743
Head	mirror polished
Handles	with multi-component grips
Style	1
Cutting capacities medium hard wire (diameter) Ø mm	0,8
Cutting capacities hard wire (diameter) Ø mm	
Cutting capacities soft wire (diameter) Ø mm	1,4
B mm	6,0
D mm	7,0
C mm	16,0
A mm	11,0
Length mm	115
Net weight g	91

technical change and errors excepted

