

71 01 200

KNIPEX CoBolt® Compact Bolt Cutters



- Precision cutting edges for soft and hard wire as well as piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Most efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- Improved cutting performance
- Micro-structured cutting edge allows easy cutting of large cross-sections
- With gripping surface below the joint for gripping and pulling wires with a diameter as from 1.0 mm



60 % less effort required compared to conventional high-leverage diagonal cutters

The ingenious lever-action mechanism ensures an extremely favourable lever ratio with very little friction. The cutting force over 30 times higher than the hand force applied.

Article No.	71 01 200
EAN	4003773033165
Pliers	black atramentized
Handles	plastic coated
Style	0
Cutting capacities medium hard wire (diameter) Ø mm	5,2
Cutting capacities hard wire (diameter) Ø mm	4,0
Cutting capacities piano wire (diameter) Ø mm	3,6
Cutting capacities soft wire (diameter) Ø mm	6,0
Length mm	200
Net weight g	335



71 01/02/12 200 and 71 31/32 200

technical change and errors excepted

