

71 02 200 T

KNIPEX CoBolt® Compact Bolt Cutters with tether attachment point



- Precision cutting edges for soft and hard wire as well as piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Most efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
- Improved cutting performance
- Micro-structured cutting edge allows easy cutting of large cross-sections
- With gripping surface below the joint for gripping and pulling wires with a diameter as from 1.0 mm
- With slim multi-component grips without collar for better handling and easier transport
- With large contact surface on the handles for better allotment of pressure and more comfort at work
- Pliers with tether attachment point for mounting a fall protection

60 % less effort required compared to conventional high-leverage diagonal cutters

The ingenious lever-action mechanism ensures an extremely favourable lever ratio with very little friction. The cutting force over 30 times higher than the hand force applied.

Article No.	71 02 200 T	✘
EAN	4003773080046	
Pliers	black atramentized	
Handles	with slim multi-component grips, with integrated tether attachment point for a tool tether	
Style	0	
Cutting capacities medium hard wire (diameter) Ø mm	5,2	
Cutting capacities hard wire (diameter) Ø mm	4,0	
Cutting capacities piano wire (diameter) Ø mm	3,6	
Cutting capacities soft wire (diameter) Ø mm	6,0	
Length mm	200	
Net weight g	375	



71 01/02/12 200 and 71 31/32 200

technical change and errors excepted