

71 32 200

KNIPEX CoBolt® Compact Bolt Cutters



- Precision cutting edges for soft and hard wire as well as piano wire
- Cuts bolts, nails, rivets, etc. up to 5.2 mm dia.
- Most efficient joint design ensures exceptional cutting performance with little effort
- Cutting edges additionally induction hardened, cutting edge hardness approx. 64 HRC
- Chrome vanadium heavy-duty steel, forged, multi stage oil-hardened
 - Style: the recess in the blade allows easier cutting of thicker wires, e. g. for anchor bolts in false ceilings
- Opening spring and locking device are integrated in the handles also for comfortable work and protected transport
- With gripping surface below the joint for gripping and pulling wires with a diameter as from 1.0 mm

60 % less effort required compared to conventional high-leverage diagonal cutters

The ingenious lever-action mechanism ensures an extremely favourable lever ratio with very little friction. The cutting force over 30 times higher than the hand force applied.

Article No.	71 32 200
EAN	4003773066880
Pliers	black atramentized
Handles	with slim multi-component grips
Style	3
Cutting capacities medium hard wire (diameter) Ø mm	5,2
Cutting capacities hard wire (diameter) Ø mm	4,0
Cutting capacities piano wire (diameter) Ø mm	3,6
Cutting capacities soft wire (diameter) Ø mm	6,0
Length mm	200
Net weight g	370



71 31/32/41 200: The cutting edge recess near the joint holds thicker wires in a favourable cutting position (optimum lever ratio). The re-positioning that is usual with bolt cutters is not needed here.



71 01/02/12 200 and 71 31/32 200



Opening spring and transport lock

technical change and errors excepted

