

87 51 250

KNIPEX Cobra® ES Water Pump Pliers extra-slim



- Ideal for service, maintenance and equipment repair, in automotive and general industry
- Long, narrow jaws
- Particularly good access to the workpiece due to very slim construction of head and joint area
- Firm grip also on flat material due to three-point rest
- Push the button for adjustment on the workpiece
- Fine adjustment for optimum adaptation to different sizes of workpieces and a comfortable handle width
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Box-joint design for high stability due to double guide
- Reliable catching of the hinge bolt: no unintentional shifting
- Favourable lever action: optimum transmission of force
- Guard prevents operators' fingers being pinched
- Chrome vanadium electric steel, forged, multi stage oil-hardened

Due to the increasing compactness of components and machines the workspace becomes more confined. However, the requirements on the gripping force and capacity of the tools do not decrease on the other hand. KNIPEX-"Cobra" ES allows powerful gripping in confined areas.

Article No.	87 51 250
EAN	4003773061267
Pliers	grey atramentized
Head	polished
Handles	with non-slip plastic coating
max. gripping depth mm	42,0
Adjustment positions	19
max. parallel opening width mm	37,0
Capacity for pipes, inches (diameter) Ø Inch	1 1/4
Capacities for pipes (diameter) Ø mm	32
Capacities for nuts mm	34
Length mm	250
Net weight g	328




Grips nuts up to 34 mm (1 5/8") across flats



Very slim design in the complete head and joint area (compared to conventional water pump pliers)




Optimum access to the workpiece. Ideal for service, maintenance and equipment repair, in automotive and general industry



Fine adjustment by pushing a button: fast and comfortable.

technical change and errors excepted



Spare Parts

Article No.	EAN	
87 09 01	4003773074724	Assortment of spare parts for adjustment for 86/87 250/300 (without 87 2)