

90 22 01 SB

KNIPEX TwistCut Corrugated Pipe Cutter



- For corrugated pipes with Ø of 13 - 32 mm
- For cutting empty or ready-assembled corrugated pipes to length
- Application in the electrical and construction trades and for plumbing work
- Recessed blades prevent injuries
- Exact, flush cut, without damaging the internal cables
- Cut on the outside of fluting - no sharp raw edge inside the corrugated pipe
- Fast and reliable work
- Simple insertion of the corrugated pipe for reliable and simple cutting: no waste
- In the case of thick-walled corrugated pipes, reapply after the circular cut just behind the cut, and break off the corrugated pipe
- Slim and ergonomically shaped for work in poorly accessible areas
- Double-sided guide for a precise cut
- Body made of stable polyamide compound plastic



Internal cables cannot be damaged when cutting the corrugated pipes externally on the ridge. As a result, the inner pipe end at the cut point always indicates a radius, so that no line is damaged during subsequent movements of the conductors or when inserting a new or additional conductor.

| | |
|---|---------------|
| Article No. | 90 22 01 SB |
| EAN | 4003773082286 |
| Cutting capacities (diameter) Ø mm | 13 - 32 |
| Length mm | 100 |
| Net weight g | 47 |



Also for protective pipes on aluminium composite pipes in plumbing, up to a diameter of 32 mm



Convenient handling due to fastener with locking device and opening by means of internal spring



Easy to use: press KNIPEX TwistCut together, turn with slight pressure, done

technical change and errors excepted