

95 05 165

Cable Shears



- Not suitable for steel wire and hard drawn copper conductors
- Precision ground, hardened blades
- No crushing, slight deformation of the cable only
- Guard prevents operators' fingers being pinched
- Adjustable bolted joint
- Shears body: surgical steel, stainless, vacuum-hardened
- Handles: plastic, impact-proof
- Cuts cables up to 10 mm dia. / 24 mm²
- With opening spring and locking device
- Blades made of stainless steel
- Oil-hardened and tempered

Article No.	95 05 165
EAN	4003773019596
Head	polished
Handles	plastic coated
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	10
Cutting capacity copper cable, multiple-stranded mm²	24
AWG	3
Length mm	165
Net weight g	111

technical change and errors excepted

