

# 95 06 230

## Cable Shears



- For cutting copper and aluminium cables
- Not suitable for steel wire and hard drawn copper conductors
- Precision ground, hardened blades
- No crushing, slight deformation of the cable only
- With guard
- Adjustable bolted joint
- Shears body: surgical steel, stainless, vacuum-hardened
- Handles: plastic, impact-proof
- For copper single conductors up to 16 mm<sup>2</sup>, multiple stranded wires up to 50 mm<sup>2</sup>, fine stranded up to 70 mm<sup>2</sup> and aluminium conductors multiple stranded wires up to 70 mm<sup>2</sup>
- Easy cutting with one-hand operation due to high transmission ratio
- Stainless - special grade - steel, oil-hardened and tempered

<b>Article No.</b>	95 06 230
<b>EAN</b>	4003773006305
<b>Head</b>	polished
<b>Handles</b>	plastic insulated, VDE-tested
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Cutting capacity copper cable, multiple-stranded (diameter) Ø mm</b>	16
<b>Cutting capacity copper cable, multiple-stranded mm<sup>2</sup></b>	50
<b>AWG</b>	1/0
<b>Length mm</b>	230
<b>Net weight g</b>	274

technical change and errors excepted

