


95 31 280

Cable Cutter (ratchet action)



- For cutting copper and aluminium single conductors as well as multiple stranded cables
- Not suitable for steel wire and wire ropes
- Precision ground, hardened blades
- Clean and smooth cut without crushing and deformation
- One-hand operation using ratchet principle
- Little handforce required due to very high transmission ratio
- Two-stage ratchet drive for easy cutting
- Simple handling as a result of low weight and compact design - can be used even in confined areas
- Guard prevents operators' fingers being pinched
- High-grade special tool steel, forged, oil-hardened
- Fixed handle with support area for putting down the pliers when cutting
- Suitable for aluminium sector cable up to 4 x 150 mm²



Article No.	95 31 280
EAN	4003773043942
Tool	black lacquered
Handles	with multi-component grips
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	52
Cutting capacity copper cable, multiple-stranded mm²	380
MCM	750
Length mm	280
Net weight g	860



95 31 280: Large cutting capacity: maximum 52 mm dia. / 380 mm²



Ratchet principle and two-stage ratchet drive for easier cutting



95 31 250/280: fixed handle with support area as an aid to position the cutters on a flat surface

technical change and errors excepted



Spare Parts

Article No.	EAN	
95 39 03	4003773039129	Movable handle (3) for 95 31 250/280
95 39 04 280	4003773032472	Feed pawl
95 39 05	4003773039174	Catch (5) for 95 31 250/280
95 39 06	4003773039181	Torsion spring (6) for 95 31 250/280
95 39 07	4003773039198	Pressure spring (7) for 95 31 250/280
95 39 08	4003773039204	Barrel spring for 95 31 250/280
95 39 09	4003773039228	Set of catches (9) for 95 31 250/280

95 39 10 97 N	4003773032441	Cover plate neutral
95 39 11	4003773039259	Joint axis (11) for 95 31 250/280
95 39 12 97	4003773032458	Set of distance bolts 3-piece
95 39 13 97	4003773032465	Set of lock nuts
95 39 280	4003773025283	Movable spare blade for 95 31 280 / 95 36 280 ratchet action