

95 32 100

Cable Cutter (ratchet action)

with telescopic handles



- For copper and aluminium single conductors as well as multiple stranded cables - also with hard rubber or plastic sheath
- Not suitable for steel wire and wire ropes
- Also suitable for cables with iron sheath reinforcement
- Little hand force required for cutting due to optimum transmission ratio
- High cutting capacity due to two-hand operation and ratchet action
- The blade can be opened in any cutting position
- Handle length with multiple position adjustment from 400 - 610 mm (short transport length, individual adaptation to working conditions)
- Blade: special-quality high-grade tool steel, oil-hardened
- Handles: high-strength oval aluminium tubing



- Tool length: 650 - 860 mm
- Weight only 4980 g

Article No.	95 32 100
EAN	4003773071570
Head	burnished
Handles	with multi-component grips
Cutting capacity copper cable, multiple-stranded (diameter) Ø mm	100
Cutting capacity copper cable, multiple-stranded mm ²	960
MCM	1900
Length mm	680
Net weight g	4980



technical change and errors excepted



Spare Parts

Article No.	EAN	
95 39 870	4003773025306	Movable spare blade for 95 31 870 / 95 32 100 (ratchet action)