

95 32 340 SR

ACSR Cable Cutter (ratchet action)

for cables with a steel core



- Handy. Compact. Sturdy.
- Extremely robust design.
- Cuts through aluminium conductor cable with steel core up to a diameter of 32 mm in one or two-handed operation
- Cutters with precision cut and induction hardened cutting edge
- Two-stage ratchet drive for easy cutting
- Less physical effort due to very high transmission ratio
- Fixed handle with support area for putting down the pliers when cutting
- Locking mechanism for transporting with safely closed handles
- Special high grade tool steel, multi stage oil-hardened



Article No.	95 32 340 SR
EAN	4003773081241
Tool	burnished
Handles	with multi-component grips
Diameter mm	32
MCM	477
Inch diameter Inch	1 1/4
Length mm	340
Net weight g	1300



The strong "flange" on the handle can be used as a practical support surface when cutting larger diameters



Enormous power with a weight of just 1300 g



The outside of these cables consists of light, highly conductive aluminium wire, and the core of extremely non-stretch galvanised steel wires

technical change and errors excepted

Spare Parts

Article No.	EAN	
95 39 340 01	4003773081340	Pivot cutter repair kit for 95 32 340 SR