

# 97 52 65 DG

## Four-Mandrel Crimping Pliers for turned contacts



- For crimping turned contacts
- Four-mandrel crimping for top-quality crimping connections
- Mandrel gauge to check the basic setting
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Optimum transmission of force due to highly effective lever action for fatigue-reduced operation
- High operation comfort thanks to handy shape
- Chrome vanadium electric steel in special quality, oil-hardened
- Crimping capacity can be adjusted in increments of 0.01 mm
- With digital display of the preset crimping capacities and possibility of re-calibration via RESET function with electronic wear monitoring
- Adjustment in mm, inches or comparable selection positions according to MIL
- With table for calculating the settings
- Pliers in a plastic case with foam insert and standard locator for precise positioning of the contacts

Turned contacts are used for particularly demanding plug-type connections, e.g. in medical industry and aeronautics. Extremely reliable crimping connections can be achieved only with pliers that work with absolute precision and maintain the required crimping depth in the 1/100 mm range.

<b>Article No.</b>	97 52 65 DG	<input checked="" type="checkbox"/>
<b>EAN</b>	4003773063216	<input checked="" type="checkbox"/>
<b>Pliers</b>	chrome plated	<input checked="" type="checkbox"/>
<b>Handles</b>	with multi-component grips	<input checked="" type="checkbox"/>
<b>Applications</b>	turned contacts (Harting; Ilme; Phoenix; Amphenol; Walther; HTS; Contact; Weidmüller)	<input checked="" type="checkbox"/>
<b>Capacity in square millimetres mm<sup>2</sup></b>	0,14 - 6,0	<input checked="" type="checkbox"/>
<b>Number of crimping positions</b>	1	<input checked="" type="checkbox"/>
<b>Max. contact diameter mm</b>	7,5	<input checked="" type="checkbox"/>
<b>AWG</b>	25 - 10	<input checked="" type="checkbox"/>
<b>Length mm</b>	250	<input checked="" type="checkbox"/>
<b>Net weight g</b>	633	<input checked="" type="checkbox"/>

multi-functional digital display, adjustment in mm, inch or comparable selection positions according to MIL

technical change and errors excepted



### Accessories

<b>Article No.</b>	<b>EAN</b>	
--------------------	------------	--

---

97 59 65 2	4003773071600	Universal Locator for 97 52 65 / 97 52 65 A / 97 52 65 DG / 97 52 65 DG A
------------	---------------	---