

98 07 250

Adjustable Wrench adjustable



- Parallel smooth gripping jaws
- Continuously variable gripping width
- With scaling for presetting the width apart from the workpiece
- Chrome Vanadium steel



Article No.	98 07 250
EAN	4003773071518
Tool	chrome plated
Handle	with dipped insulation
Jaw width mm	8,0
Head width mm	16,0
Width mm	73,0
Depth mm	20,0
Capacities for nuts mm	30
Capacities for nuts Inch	1 1/8
Length mm	260
Net weight g	500



technical change and errors excepted

