

Compatible with a number of Android Smartphones, the Z360m transforms your USB-C device into a powerful 360° camera using the Mini360 App. Easily take exceptional photos, FHD video or live stream on social media.

Featuring two 210° fisheye lenses, the Z360m effortlessly captures details you never thought possible. It's perfectly pocket-sized and lightweight, making it the ultimate mobile imaging accessory.

Lose yourself in the world of 360° content. It's a great way to relive your special moments.





Key Features

- Effortlessly shoot full HD Video
- Capture 360° photos at the touch of a button
- Live stream on popular social media sites
- Small enough to fit in your pocket
- · Lightweight; only 22g
- USB Type C compatible
- Share your content using the Mini360 App
- Accessories: Quick Start Guide (EN), Camera Pouch, Strap, Wipe Cloth

Specification				Silver: Z360M-S
Image Resolution	13 Megapixels	Image Circle	Ø 3.514mm	
Image Sensor	1/3.06	ISO Sensitivity	Up to 1600	
Lens Type	Fixed focus, Fisheye	Aperture	F1.8	
Photo Format	JPEG	Operating Temp	0°c~40°c	
Video Format	MP4	Dimensions	ø 34x25.2mm	
Video Resolution	FHD@30fps/HD@30fps	Weight	22g	
USB	Type C			

PRAKTICA

Z360m Specification

Image Sensor 1/3.06"

Effective Pixels Approx. 13.28 Megapixels
Total Pixel Approx. 13.48 Megapixels

Lens Type Fixed focus, Fisheye

FOV 210° x 2 Focal Length 1.05mm Image Circle Ø 3.514mm

Aperture F1.8

USB Micro USB Type C

Image Size 5376x2688

Self-Timer Off/2 sec/5 sec/10 sec

Electronic Shutter 1/6400~1/8 sec

Function Mode Broadcast/Take picture/Video

White Balance
ISO

Auto White Balance
Auto (Max. ISO 1600)

EV Compensation 0EV, -2~ +2 EV

Image File Format JPEG Video Format MP4

Video Recording FHD -1920(H)x960(V)@30fps/HD - 1280(H)x640(V)@30fps

Android Version 6.0+

Shockproof 1m

Operating Temp $0^{\circ}c \sim 40^{\circ}c$

Dimensions ø34x25.2mm

Weight 22g

Accessories Quick Start Guide (EN), Camera Pouch, Strap, Wipe Cloth

