

PIXMA TS3150

A USER FRIENDLY, AFFORDABLE PRINTER WITH SMART CONNECTIVITY

Enjoy crisp text and vivid, borderless photo printing, straight from your Smart device, Wi-Fi camera or the cloud, with this affordable PIXMA printer. Scan and copy with ease, using the intuitive 3.8cm LCD display.



KEY FEATURE

Smart device printing, scanning and copying

- Print from anywhere with convenient wireless printing, using the Canon PRINT app, AirPrint and Mopria

Stylish, durable design

- With a surface that's fingerprint and scratch resistant, this printer is practical and easy to maintain

Cost-effective XL cartridges

- Use high-capacity Canon XL ink cartridges and save up to 30% per page, compared to standard equivalents

Easy-to-use LCD screen and buttons

- Connect to your Smart device, check your settings and troubleshoot with the easy-to-use 3.8cm LCD screen.

Borderless Photo Printing

- Create vivid borderless photos up to 5x7" thanks to dye-based ink cartridges



Product Range



PIXMA TS3150 Series



PIXMA MG3650



PIXMA MG4250

PIXMA TS3150 Series

PIXMA MG3650

PIXMA MG4250

PIXMA TS5050 Series

TECHNICAL SPECIFICATIONS

PIXMA TS3150

GENERAL SPECIFICATIONS

Model Numbers

PIXMA TS3150

Functions

Wi-Fi, Print, Copy, Scan, Cloud

PRINTER SPECIFICATIONS

Print Resolution

Up to 4800^[1] x 1200 dpi

Print Technology

2 FINE Cartridges (Black and Colour)

Mono Print Speed

Approx. 7.7 ipm^[2]

Colour Print Speed

Approx. 4.0 ipm^[2]

Photo Print Speed

Borderless 10cm x 15cm : Approx. 65 seconds^[2]

Borderless Printing

Yes (13cm x 18cm, 10cm x 15cm, 13cm x 13cm)

Two Sided Printing

Manual operation

CARTRIDGES AND YIELDS

Standard Ink Cartridges

PG-545 (Black)

CL-546 (Colour)

Optional XL Ink Cartridges

PG-545XL (Black)

CL-546XL (Colour)

Cartridge Yield (Plain paper)

A4 colour documents printing^[3]

Black: 180 pages

Black XL: 400 pages

Colour: 180 pages

Colour XL: 300 pages

PAPER SUPPORT

Paper Types

Plain Paper

Envelopes

Photo Paper Plus Glossy II (PP-201)

Photo Paper Glossy "Everyday Use" (GP-501)

Maximum Paper Input Paper Sizes

Rear tray: Max. 60 sheets (plain paper)

Plain paper: A4, A5, B5, Letter, Legal

Photo paper: 10cm x 15cm, 13cm x 13cm,

13cm x 18cm

Envelopes: DL, COM10

Paper Weight

Plain paper: 64 - 105 g/m²

Canon photo paper: up to 275 g/m²

SCANNER SPECIFICATIONS

Scanner Type

CIS flatbed photo and document scanner

Scanner Resolution (Optical)

600 x 1200 dpi^[4]

A4 Scan Speed

Approx. 15 sec^[5]

Scanning Depth

Colour: RGB each 16bit/8bit

(Input / Output)

Greyscale: 16 bit/8 bit

Maximum Document Size

216mm x 297mm

COPIER SPECIFICATIONS

Copy Speed

sFCOT: Approx. 27 sec.^[6]

sESAT: Approx. 3.0 ipm^[6]

Multiple Copy

20 copies (max.)

Copy Functions

Document copying, Borderless copy

Document Size

216mm x 297mm

INTERFACE

Display Type & Size

3.8cm LCD segment mono

Interface Type - PC / Mac

Hi-Speed USB (B Port)

Wi-Fi: IEEE802.11 b/g/n

Wi-Fi Security: WPA-PSK, WPA2-PSK, WEP,

Administration password

Wireless LAN Frequency Band: 2.4GHz

Interface Type - Other

PIXMA Cloud Link

Canon PRINT Inkjet/SELPHY app

Canon Print Service Plugin (Android)

Google Cloud Print

Access Point Mode

WLAN PictBridge

Apple AirPrint

Mopria (Android)

SOFTWARE

Supported

Operating Systems

Windows 10, Windows 8.1, Windows 7 SP1

Note: For Windows, .NET Framework 4.5.2 or 4.6

is required OS X 10.10.5–OS X 10.11, macOS 10.12

Supported Mobile Systems

iOS, Android, Windows 10 Mobile

Minimum System Requirements

Software Included

Windows: 3.1GB disk space, Internet Explorer 8

Mac: Internet connection, 1.5GB disk space, Safari 5

Display: 1024 x 768 XGA

MP Driver including Scanning Utility

My Image Garden with Full HD Movie Print^[7]

Quick Menu

Easy-WebPrint EX (download)^[8]

PHYSICAL FEATURES

Weight

approx. 3.9 kg

Dimensions (W x D x H)

approx. 435mm x 316mm x 145mm

Acoustic Noise Levels

approx. 46.0dB(A)^[9]

Recommended Operating

Environment

Temperature: 15-30°C

Humidity: 10-80%RH (no dew condensation)

Power Source

AC 100-240V, 50/60Hz

Power Consumption

Off: Approx. 0.3W

Standby (connected to PC via USB): Approx. 1.7W

(scanning lamp off)

Standby (all ports connected): Approx. 1.7W

(scanning lamp is off)

Time to enter Standby mode: 11 minutes

Copying: Approx. 11W^[10]

Footnotes

¹ Ink droplets can be placed with a minimum pitch of 1/4800 inch

² A4 document print speed on plain paper is measured based on average of ESAT in Office Category Test of ISO/IEC 24734 standard.

³ Declared yield value in accordance with ISO/IEC 24711 standard. Values obtained by continuous printing.

⁴ Optical resolution is a measure of maximum hardware sampling resolution based on ISO 14473 standard. When scanning in high resolution, the maximum scan size is restricted.

⁵ Color document scan speed is measured with ISO/IEC 29183 Target A.

Scan speed indicates the time measured between pressing the scan button of the scanner driver and the on-screen status display turns off.

Scan speed may vary depending on system configuration, interface, software, scan mode settings and document size etc.

⁶ Colour document copy speed is measured based on average of sFCOT and sESAT in Performance Test of ISO/IEC 29183 standard.

⁷ Full HD Movie Print is available for MOV and MP4 movie files created by select Canon digital cameras and camcorders. Requires installation of software bundled with Canon video or digital camera, from which the movie was captured. MOV files require: ZoomBrowser EX / ImageBrowser (version 6.5 or later), MP4 files require: ImageBrowser EX (version 1.0 or later).

⁸ Easy-WebPrint EX: Internet Explorer 8, 9, 10 and 11* (for Windows) is required.

⁹ When printing ISO/JIS-SCID N2 pattern on 10x15cm Photo Paper Plus Glossy II using default settings.

¹⁰ When copying ISO/JIS-SCID N2 (printed by inkjet printer) on A4 size plain paper using default settings.

Standard disclaimers

• All specifications subject to change without notice.

• Print speed may vary depending on system configuration, interface, software, document complexity, print mode, page coverage, type of paper used etc.

• Ink yield may vary depending on texts/photos printed, applications software used, print mode and type of paper used. For yield information see www.canon-europe.com/ink/yield

• Scan speed may vary depending on system configuration, interface, software, scan mode settings and document size etc.

• Copy speed may vary depending on document complexity, copy mode, page coverage, type of paper used etc. and does not take into account warming up time.

• All brand and product names are trademarks of their respective companies.

• Microsoft, Windows and the Windows logo are trademarks, or registered trademarks of Microsoft Corporation in the United States and/or other countries.

Canon Inc.

canon.com

Canon Europe

canon-europe.com

English edition

Canon Europa NV 2017

A USER FRIENDLY, AFFORDABLE PRINTER WITH SMART CONNECTIVITY

Enjoy crisp text and vivid, borderless photo printing, straight from your Smart device, Wi-Fi camera or the cloud, with this affordable PIXMA printer. Scan and copy with ease, using the intuitive 3.8cm LCD display.

Sales Start Date: Aug 2017

PIXMA TS3150



PRODUCT DETAILS:

Product Name	Mercury Code	EAN Code	Recommended Retail Price
PIXMA TS3150	2226C008AA	4549292092899	£49.99 / €59.99

CONSUMABLES:

Product Name	Mercury Code	EAN Code
PG-545	8287B001AA	4960999974507
CL-546	8289B001AA	4960999974521
PG-545XL	8286B001AA	4960999974491
CL-546XL	8288B001AA	4960999974514
PG-545/CL-546 MULTI	8287B005AA	8714574605517
CRG PG-545XL/CL-546XL PHOTO VALUE	8286B006AA	8714574630793
CRG PG-545XL/CL-546 MULTI	8286B008AA	8714574631530

MEASUREMENT / LOGISTIC INFORMATION:

Product Name	Mercury Code	Pack type	Pack description	Quantity per pack	Length (mm)	Width (mm)	Height (mm)	Gross Weight (kg)
PIXMA TS3150	2226C006AA	EA	Each	1	487.8	195.8	398	5.4
		CT	Carton	36	988.6	1187.8	1198.5	195.8
		EP	Euro Pallet	36	988.6	1187.8	1198.5	195.8

What's in the box?

- All-in-one printer – PIXMA TS3150
- FINE Cartridges
- Power cord
- Setup CD-ROM (CD only for Windows)
- Manuals and other documents

Canon