

Part Number:0008520072

Status:Active

Overview:KK® Interconnect System - Molex

Description:KK 396 Crimp Terminal 2478, 18-24 AWG, Bag, Phosphor Bronze, Tin (Sn)

Documents:

図面 (PDF)

梱包仕様書 PS-08-50-001 (PDF)

梱包仕様書 PK-2759-001 (PDF)

RoHS Certificate of Compliance (PDF)

一般	
用途	Power, 電線対基板
Crimp Quality Equipment	有
概要	KK® Interconnect System - Molex
梱包違い製品	08-52-0071 (Reel)
製品名	KK 396, KK 508
UPC	800754225632
機械的性能/材質	
ジェンダー	フィメール
材質 - 金属部	りん青銅
材質 - 嵌合部メッキ	錫
材質 - ターミナルメッキ	錫
Net Weight	0.240/g
梱包形態	ポリ袋
嵌合部メッキ厚	2.540μm
ターミナルメッキ厚	2.540μm
実装スタイル	圧着またはコンプレッション
被覆外径	2.79mm max.
電線サイズ (AWG)	18, 20, 22, 24
Wire Size mm ²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
参考情報	
Engineering Number	2478-3- (P909)L
図面・仕様書情報	
梱包仕様書	PK-2759-001
製品仕様書	PS-08-50-001
製品図面	SD-2478



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/61/2018 (27 June

2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

2478 Series

Use With

2574 , 2139 , 41695 , 3069 , 6422 ,

5265 , 5239