

Part Number: [0433750001](#)  
 Status: Active  
 Overview: [Sabre Power Connector](#)  
 Description: Sabre Crimp Terminal, Female, 14-16 AWG, 3.30mm max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact with TPA

Documents:

[図面 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[製品仕様書 PS-44441-9999-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

一般用途コメント	Power, 電線対基板, 電線対電線 Terminal mates to 3.18mm wide x 0.51mm thick flat blade PC tab. Allows 44441 receptacle housings to comply with the UL1977 finger proof access requirement
Crimp Quality Equipment 概要	有
Product Literature Order No	<a href="#">Sabre Power Connector</a>
製品名	987650-5662
UPC	Sabre 800754365970
機械的性能/材質	
耐久挿抜回数	25
ジェンダー	フィメール
材質 - 金属部	黄銅
材質 - 嵌合部メッキ	錫
材質 - ターミナルメッキ	錫
Net Weight	0.334/g
梱包形態	リール
嵌合部メッキ厚	0.508µm
ターミナルメッキ厚	0.508µm
実装スタイル	圧着またはコンプレッション
被覆外径	3.30mm max.
電線サイズ (AWG)	14, 16
Wire Size mm <sup>2</sup>	N/A
電気的性能	
最大定格電流	18.0A
最大定格電圧	600V
Solder Process Data	
Lead-freeProcess Capability	N/A
参考情報	
図面・仕様書情報	
製品仕様書	PS-44441-9999-001
製品図面	SD-43375-0001



EU ELV  
Not Relevant

EU RoHS [China RoHS](#)  
Compliant

REACH SVHC  
Not Contained Per -  
ED/61/2018 (27 June  
2018)

Halogen-Free  
Status

Low-Halogen

For more information, please visit  
[Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series  
[43375 Series](#)

Mates With  
[43178 Male Crimp Terminals](#)

Use With  
[44441 Receptacle Housings](#)