

Part Number:0522712069

Status:Active

Overview:FFC-FPC (SMT)

Description:1.00mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Surface Mount, ZIF, Bottom Contact Style, 20 Circuits, High Barrier Packaging

Documents:

3Dモデル

図面 (PDF)

製品仕様書 PS-52271-054-001 (PDF)

圧着仕様書 AS-52271-001-001 (PDF)

梱包仕様書 SPK-52271-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
一般概要製品名UPC	
FFC-FPC (SMT)	
Easy-On	
822350052559	
機械的性能/材質	
Actuator Type	Slider
極数 (実装)	20
色 - 樹脂部	自然色
コンタクト位置	下面
耐久挿抜回数	30
難燃性	94V-0
嵌合高さ	3.00mm
材質 - 金属部	りん青銅
材質 - 嵌合部メッキ	金
材質 - ターミナルメッキ	錫
材質 - 樹脂部	ナイロン
Net Weight	847.300/mg
列数	1
実装形態	ライトアングル
位置決め	無
PCB Mounting	SMT (表面実装)
基板保持	有
梱包形態	エンボステーピング
ピッチ - 嵌合部 (インチ)	1.00mm
ピッチ - 実装部	1.00mm
基板極性	有
縦列スタック (エンド・ツー・エンド)	無
使用温度範囲	-40° to +85° C
ケーブル種別	FFC/FPC
電気的性能	
最大定格電流	0.5A
最大定格電圧	50V AC (RMS)/DC

参考情報

図面・仕様書情報

圧着仕様書AS-52271-001-001

梱包仕様書SPK-52271-002-001

製品仕様書PS-52271-054-001

製品図面SD-52271-038-001, SD-52271-039



EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/61/2018 (27 June 2018)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

52271 Series

Mates With

Molex Premo-Flex FFC. Be sure to match like plating

This document was generated on 09/21/2018
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION