

**Part Number:** [0151660427](#)  
**Status:** Active  
**Overview:** [Premo-Flex Cable Jumpers](#)  
**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 40 Circuits, 0.05m Cable Length, Tin (Sn) Plating

**Documents:**

<a href="#">図面 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">製品仕様書 PS-15166-001-001 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">梱包仕様書 PK-15166-001-001 (PDF)</a>	

一般コメント	Contacts on the same side, Type A
Crimp Quality Equipment	有
概要	<a href="#">Premo-Flex Cable Jumpers</a>
Product Literature Order No	987650-6631
製品名	Premo-Flex FFC Jumper
UPC	884982849259
機械的性能/材質	
ケーブル長	0.051m
極数 (実装)	40
極数 (最大)	40
Net Weight	1.000/g
梱包形態	ポリ袋
ピッチ - 実装部	0.50mm
使用温度範囲	-40° to +105° C
電線サイズ (AWG)	N/A
ケーブル種別	FFC
電気的性能	
最大定格電流	0.5A
最大定格電圧	60V AC
参考情報	
図面・仕様書情報	
梱包仕様書	PK-15166-001-001
製品仕様書	PS-15166-001-001
製品図面	SD-15166-001



Series image - Reference only

EU ELV  
Not Relevant

EU RoHS China RoHS

Compliant

REACH SVHC

Not Contained Per -  
ED/61/2018 (27 June  
2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product  
environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for  
any non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series  
[15166 Series](#)

Use With  
<a href="http://www.molex.com/product/ffc">Molex FFC - FPC connector</a>. Be  
sure to match like plating.