

Part Number: [0525590652](#)
Status: Active
Overview: [FFC-FPC \(SMT\)](#)
Description: 0.50mm Pitch Easy-On FFC/FPC Connector, Vertical, Surface Mount, ZIF, 6 Circuits, Gold (Au) Contact Plating, High Barrier Packaging

Documents:

[3Dモデル](#) [圧着仕様書 AS-52559-001-001 \(PDF\)](#)
[図面 \(PDF\)](#) [梱包仕様書 SPK-52559-003-001 \(PDF\)](#)
[製品仕様書 PS-52559-013-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL	E29179
一般	
概要	FFC-FPC (SMT)
製品名	Easy-On
UPC	822348533916
機械的性能/材質	
Actuator Type	Slider
極数 (実装)	6
コンタクト位置	N/A
耐久挿抜回数	20
難燃性	94V-0
嵌合高さ	3.90mm
材質 - 金属部	りん青銅
材質 - 嵌合部メッキ	金
材質 - ターミナルメッキ	錫
材質 - 樹脂部	ナイロン
Net Weight	133.456/mg
列数	1
実装形態	ストレート
位置決め	無
PCB Mounting	SMT (表面実装)
基板保持	有
梱包形態	エンボステーピング
ピッチ - 嵌合部 (インチ)	0.50mm
基板極性	無
縦列スタック (エンド・ツー・エンド)	無
使用温度範囲	-40° to +85° C
ケーブル種別	FFC/FPC
電気的性能	
最大定格電流	0.5A
最大定格電圧	50V AC (RMS)/DC
参考情報	
図面・仕様書情報	
圧着仕様書	AS-52559-001-001
梱包仕様書	SPK-52559-003-001
製品仕様書	PS-52559-013-001
製品図面	SD-52559-049-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit
[Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[52559 Series](#)

Mates With

Molex Premo-Flex FFC. Be sure to match like plating

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION