

Part Number: [0527452097](#)
Status: Active
Overview: [FFC-FPC \(SMT\)](#)
Description: 0.50mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Surface Mount, ZIF, Top Contact Style, 20 Circuits, Gold (Au) Contact Plating, High Barrier Packaging

Documents:

[3Dモデル](#) [圧着仕様書 AS-52745-001-001 \(PDF\)](#)
[図面 \(PDF\)](#) [梱包仕様書 SPK-52745-002-001 \(PDF\)](#)
[製品仕様書 PS-52745-051-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL	E29179
一般	
概要	FFC-FPC (SMT)
製品名	Easy-On
UPC	822348250585
機械的性能/材質	
Actuator Type	Slider
極数 (実装)	20
色 - 樹脂部	黒色, 白色
コンタクト位置	トップ
耐久挿抜回数	20
難燃性	94V-0
嵌合高さ	2.00mm
材質 - 金属部	りん青銅
材質 - 嵌合部メッキ	金
材質 - ターミナルメッキ	金
Net Weight	242.510/mg
列数	1
実装形態	ライトアングル
位置決め	無
PCB Mounting	SMT (表面実装)
基板保持	有
梱包形態	エンボステーピング
ピッチ - 嵌合部 (インチ)	0.50mm
基板極性	有
縦列スタック (エンド・ツー・エンド)	無
使用温度範囲	-40° to +85° C
ケーブル種別	FFC/FPC
電気的性能	
最大定格電流	0.5A
最大定格電圧	50V
参考情報	
図面・仕様書情報	
圧着仕様書	AS-52745-001-001
梱包仕様書	SPK-52745-002-001
製品仕様書	PS-52745-051-001
製品図面	SD-52745-050-001, SD-52745-051



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

**Halogen-Free
Status**

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for
any non-product compliance questions.

China ROHS

ELV

Prop65

RoHS Phthalates

Green Image

Not Relevant

Compliant

Not Contained

Search Parts in this Series
[52745 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION