

Part Number: [0701070003](#)  
 Status: Active  
 Overview: [SL Modular Connectors](#)  
 Description: SL Wire-to-Wire Crimp Housing, Single Row, Version A, without Mounting Ears, 4 Circuits, Black

Documents:

[3Dモデル](#) [製品仕様書 TS-70541-001-001 \(PDF\)](#)  
[図面 \(PDF\)](#) [梱包仕様書 PK-70107-100 \(PDF\)](#)  
[製品仕様書 PS-70400-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980  
 UL E29179

一般用途コメント  
 概要  
 製品名  
 UPC

Signal, 電線対電線  
 Version A without Mounting Ears  
[SL Modular Connectors](#)  
 SL  
 800753560796

機械的性能/材質

極数 (最大) 4  
 色 - 樹脂部 黒色  
 難燃性 94V-0  
 ジェンダー プラグ  
 Glow-Wire Capable 無  
 嵌合ロック 有  
 材質 - 樹脂部 Polyester  
 Net Weight 0.840/g  
 列数 1  
 梱包形態 ポリ袋  
 パネルマウント 無  
 ピッチ - 嵌合部 (インチ) 2.54mm  
 嵌合極性 有  
 縦列スタック (エンド・ツー・エンド) 無  
 使用温度範囲 -40° to +105° C

参考情報

図面・仕様書情報  
 梱包仕様書 PK-70107-100  
 製品仕様書 PS-70400-001, TS-70541-001-001  
 製品図面 SD-70107-0001-0024



Series image - Reference only

EU ELV  
 Not Relevant

EU RoHS [China RoHS](#)

Compliant  
[REACH SVHC](#)  
 Not Contained Per -  
 ED/61/2018 (27 June  
 2018)

[Halogen-Free](#)  
 Status

Not Low-Halogen

For more information, please visit  
[Contact US](#)

China ROHS [Green Image](#)  
 ELV [Not Relevant](#)  
 RoHS Phthalates [Not Contained](#)

Search Parts in this Series  
[70107 Series](#)

Mates With  
[70066](#) SL Crimp Housing A, G and D  
 (Notes: Version C and H will not mate  
 to the 70107 housing series), [70400](#)  
 SL Insulation Displacement Connector  
 Assembly, Version G Housing, [70430](#) SL  
 Single Row Receptacle, Version G

Use With  
[70021](#) SL Crimp Terminal