

Part Number: [0734156180](#)  
 Status: Active  
 Overview: [SMPM and SMP RF Connectors](#)  
 Description: 50 Ohms, SMP Surface Mount Plug, Limited Detent, One Piece Per Bag

Documents:

[3Dモデル](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[図面 \(PDF\)](#)

一般概要	<a href="#">SMPM and SMP RF Connectors</a>
製品名	SMP
スタイル	基板用ストレート
タイプ	Subminiature
UPC	800756689494
ケーブル種別	N/A
機械的性能/材質	
ジェンダー	プラグ
嵌合キー	無
Net Weight	0.279/g
実装形態	ストレート
PCB Mounting	SMT (表面実装)
梱包形態	ポリ袋
パネルマウント	無
パネルマウント方法	N/A
電気的性能	
Frequency	40 GHz
インピーダンス	50 Ω
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	REFLOW
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	260
参考情報	
図面・仕様書情報	
製品図面	SD-73415-618-001, SD-85305-0232-001



EU ELV  
Not Relevant

EU RoHS China RoHS

Compliant with  
Exemption 6(c)

REACH SVHC  
Contained Per -  
ED/61/2018 (27 June  
2018)  
鉛

Halogen-Free  
Status

Low-Halogen

Need more information on product  
environmental compliance?

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for  
any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
Prop65	Duty-To-Declare
PropRisk	Cancer
PropRisk	Developmental toxicity
PropRisk	Reproductive toxicity
PropSub	Lead and its compounds
RoHS Phthalates	Not Contained

Search Parts in this Series  
[73300 Series](#)