

Part Number: [0433750001](#)
Status: Active
Overview: [Sabre Power Connector](#)
Description: Sabre Crimp Terminal, Female, 14-16 AWG, 3.30mm max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact with TPA

Documents:

[도면 \(PDF\)](#) [RoHS 증명서\(PDF\)](#)
[제품규격 PS-44441-9999-001 \(PDF\)](#) [Product Literature \(PDF\)](#)

일반적 특성

적용제품 설명 Power, 와이어 대 보드, 와이어 대 와이어 Terminal mates to 3.18mm wide x 0.51mm thick flat blade PC tab. Allows 44441 receptacle housings to comply with the UL1977 finger proof access requirement

Crimp Quality Equipment Yes
전체보기 [Sabre Power Connector](#)
Product Literature Order No 987650-5662
제품명 Sabre
UPC 800754365970

물리적 특성

내구성(최대 메이팅 사이클) 25
암수구분 암
원재료 - 메탈 황동
원재료 - 도금부 주석
원재료 - 도금부 터미네이션 주석
Net Weight 0.334/g
포장타입 릴 (Reel)
최소도금: 결합 0.508µm
최소 도금: 터미네이션 0.508µm
터미네이션 결합방식 크립프 또는 압착
와이어 절연 두께 3.30mm max.
와이어 사이즈 (AWG) 14, 16
와이어 사이즈 mm² N/A

전기적 특성

전류 - 접촉 당 최대 출력 18.0A
최대전압 600V

납땀 프로세스 정보

Lead-freeProcess Capability N/A

원재료 정보

참고 - 도면번호
제품규격 PS-44441-9999-001
도면 SD-43375-0001



Series image - Reference only

[EU ELV](#)
Not Relevant

[EU RoHS](#) [China RoHS](#)

[Compliant](#)
[REACH SVHC](#)
 Not Contained Per -
 ED/61/2018 (27 June
 2018)

[Halogen-Free](#)
[Status](#)

[Low-Halogen](#)

For more information, please visit
[Contact US](#)

[China ROHS](#) [Green Image](#)
[ELV](#) [Not Relevant](#)
[RoHS Phthalates](#) [Not Contained](#)

Search Parts in this Series
[43375](#) Series

Mates With
[43178](#) Male Crimp Terminals

Use With
[44441](#) Receptacle Housings