

Part Number: [5034801000](#)
Status: Active
Overview: [FFC-FPC \(SMT\)](#)
Description: 0.50mm Pitch Easy-On Back Flip FPC Connector, 1.00mm Height, Right-Angle, Surface Mount, Dual Contact Style, 10 Circuits

Documents:

[3D 모델](#) [Packaging Specification SPK-503480-001 \(PDF\)](#)
[도면 \(PDF\)](#) [RoHS 증명서 \(PDF\)](#)
[제품규격 PS-503480-001 \(PDF\)](#)

Agency Certification

UL	E29179
일반적 특성	
설명	Black Actuator
전체보기	FFC-FPC (SMT)
제품명	Easy-On
UPC	884982040854
물리적 특성	
Actuator Type	Flip
회로수	10
색상 - Resin	Natural (White)
결합위치	듀얼
내구성(최대 메이팅 사이클)	10
난연성	94V-0
Mated Height	1.00mm
원재료 - 메탈	인칭동
원재료 - 도금부	Gold over Nickel
원재료 - 도금부 터미네이션	Gold over Nickel
원재료 - 플라스틱	Liquid Crystal Polymer
Net Weight	39.191/mg
열 수	1
방향성	직각
PCB 고정위치	No
PCB 마운팅	표면실장
PCB 유지력	Yes
포장타입	엠보스드 테이프 / 릴
피치 - 결합부	0.50mm
PCB 오삽입 장치	Yes
End-to-End 연결형	No
사용온도 범위	-40° to +85°C
와이어/케이블 타입	FPC용
전기적 특성	
전류 - 접촉 당 최대 출력	0.5A
최대전압	50V AC (RMS)/DC
납땜 프로세스 정보	
Duration at Max. Process Temperature (seconds)	003
Lead-free Process Capability	REFLOW
Max. Cycles at Max. Process Temperature	002
Process Temperature max. C	250

원재료 정보

참고 - 도면번호



Series image - Reference only

EU ELV
Not Relevant

EU RoHS China RoHS

Compliant

[REACH SVHC](#)

Not Contained Per -
ED/61/2018 (27 June
2018)

[Halogen-Free](#)

Status

Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for
any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series
[503480 Series](#)

Packaging Specification
제품규격
도면

SPK-503480-001
PS-503480-001
SD-503480-001, SD-503480-002

This document was generated on 09/03/2018
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION