

Part Number: [0527462071](#)
Status: Active
Overview: [FFC-FPC \(SMT\)](#)
Description: 0.50mm Pitch Easy-On FFC/FPC Connector, Right-Angle, Surface Mount, ZIF, Bottom Contact Style, 20 Circuits, Gold Contact Plating, High Barrier Packaging

Documents:

3D 모델 [Packaging Specification SPK-52746-002-001 \(PDF\)](#)
도면 (PDF) [RoHS 증명서\(PDF\)](#)
제품규격 PS-52746-015-001 (PDF)

Agency Certification

CSA LR19980
UL E29179

일반적 특성

전체보기 [FFC-FPC \(SMT\)](#)
제품명 Easy-On
UPC 822348157464

물리적 특성

Actuator Type Slider
회로수 20
결합위치 하면
내구성(최대 메이팅 사이클) 20
난연성 94V-0
Mated Height 2.00mm
원재료 - 메탈 인칭동
원재료 - 도금부 금
원재료 - 도금부 터미네이션 금
Net Weight 228.960/mg
열 수 1
방향성 직각
PCB 고정위치 No
PCB 마운팅 표면실장
PCB 유지력 Yes
포장타입 엠보스드 테이프 / 릴
피치 - 결합부 0.50mm
PCB 오삽입 장치 Yes
End-to-End 연결형 No
사용온도 범위 -40° to +85°C
와이어/케이블 타입 FFC/FPC

전기적 특성

전류 - 접촉 당 최대 출력 0.5A
최대전압 50V

원재료 정보

참고 - 도면번호

Packaging Specification SPK-52746-002-001
제품규격 PS-52746-015-001
도면 SD-52746-024, SD-52746-025-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for
any non-product compliance questions.

China ROHS

ELV

Prop65

RoHS Phthalates

Green Image

Not Relevant

Compliant

Not Contained

Search Parts in this Series
[52746 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION