

Part Number: [0701070003](#)
 Status: Active
 Overview: [SL Modular Connectors](#)
 Description: SL Wire-to-Wire Crimp Housing, Single Row, Version A, without Mounting Ears, 4 Circuits, Black

Documents:

3D 모델 [제품규격 TS-70541-001-001 \(PDF\)](#)
 도면 (PDF) [Packaging Specification PK-70107-100 \(PDF\)](#)
 제품규격 PS-70400-001 (PDF) [RoHS 증명서\(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

일반적 특성

적용제품 Signal, 와이어 대 와이어
 설명 Version A without Mounting Ears
 전체보기 [SL Modular Connectors](#)
 제품명 SL
 UPC 800753560796

물리적 특성

최대 회로수 4
 색상 - Resin Black
 난연성 94V-0
 압수구분 플러그
 Glow-Wire Capable No
 결합제품 잠금장치 Yes
 원재료 - 플라스틱 Polyester
 Net Weight 0.840/g
 열 수 1
 포장타입 백 (Bag)
 패널마운트 No
 피치 - 결합부 2.54mm
 결합제품 오삽입 장치 Yes
 End-to-End 연결형 No
 사용온도 범위 -40° to +105°C

원재료 정보

참고 - 도면번호
 Packaging Specification PK-70107-100
 제품규격 PS-70400-001, TS-70541-001-001
 도면 SD-70107-0001-0024



Series image - Reference only

EU ELV
 Not Relevant

EU RoHS China RoHS

Compliant
 REACH SVHC
 Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free
 Status

Not Low-Halogen

For more information, please visit
 Contact US

China ROHS Green Image
 ELV Not Relevant
 RoHS Phthalates Not Contained

Search Parts in this Series
[70107 Series](#)

Mates With
[70066](#) SL Crimp Housing A, G and D
 (Notes: Version C and H will not mate
 to the 70107 housing series), [70400](#)
 SL Insulation Displacement Connector
 Assembly, Version G Housing, [70430](#) SL
 Single Row Receptacle, Version G

Use With
[70021](#) SL Crimp Terminal